

Enerquip Code 7 Single Round Filter Housings


When Schedule Counts

Overview

Enerquip's code 7 filter housings are offered in heights of 5" and 10" in the single round design configuration. These code 7 filter housings come with a recessed base design and an all 316L stainless steel construction on the product contact side. All housings come with a choice of internal surface finish and a choice of inlet, outlet, vent, and drain connections.

Features and Options

- T-Line and I-Line design available with recessed base design
- 316L product contact side construction
- 10" and 5" single round designs
- 32 Ra mechanical polish OD; 20 Ra Mechanical polish ID
- Factory pressure tested and passivated



FILTER HOUSING STANDARD OFFERING

PART NUMBER	DESCRIPTION	FINISH	PRICE
5T75P150N	5" T-line Filter housing, .75" TC Inlet/Outlet, 1.5" TC gage port, Plunger drain valve, no vent	20 Ra	\$2,500
5T100P150N	5" T-line Filter housing, 1" TC Inlet/Outlet, 1.5" TC gage port, Plunger drain valve, no vent	20 Ra	\$2,525
10T100P150N	10" T-line Filter housing, 1" TC Inlet/Outlet, 1.5" TC gage port, Plunger drain valve, no vent	20 Ra	\$2,610
5I150P150N	5" I-line Filter Housing, 1.5" TC Inlet/Outlet, Plunger drain valve, no vent	20 Ra	\$2,075
10I150P150N	10" I-line Filter Housing, 1.5" TC Inlet/Outlet, Plunger drain valve, no vent	20 Ra	\$2,225

FILTER HOUSING STANDARD OFFERING

PART NUMBER	DESCRIPTION	FINISH	PRICE
- EP	Optional Electropolish ID finish	15 Ra EP	\$300
- D	Optional Documentation to include: Mtr's, Weld Logs, Gasket COC's		\$480
	Customized inlets, outlets, vent and drain connections		TBD

10" T-Line
Filter housing with
.75" inlet and outlet
connections and
a 1.50" gage port.
Includes a plunger
valve on the outlet



10" T-Line
Filter housing with
1.50" inlet and
outlet connections.
Includes a plunger
valve on the outlet
and no accessory
on the inlet.



1009

Southgate Process Equipment, Inc. is an authorized representative for Enerquip, LLC

87 Hickory Springs Industrial Drive, Canton, GA 30115

Phone: (770) 345-0010 | Email: Sales@southgateprocess.com | Website: www.Southgateprocess.com




Sanitary Stainless Steel Membrane Housings







MODEL SELECTION GUIDE



Inlet/Outlet Size

50 = .50" Sanitary Ferrule 75 = .75" Sanitary Ferrule 100 = 1" Sanitary Ferrule 150 = 1.5" Sanitary Ferrule

Drain Type

P = Plunger Valve

N = None

F = .50" Sanitary Ferrule -N/A on .50" inlet/outlet

Vent Type

N = No Vent

F = .50" Sanitary Ferrule

Documentation

Blank = No Documentation = Mtr's, Weld Logs, Finish

Certificate & Gasket COC











Southgate Process Equipment, Inc.

87 Hickory Springs Industrial Dr. Canton, GA 30115 Phone: (770) 345-0010 Email: Sales@southgateprocess.com Website: www.southgateprocess.com

